

All HE13/HE14 IDC Receptacle, DRST, AWG24-2 (7)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 281743-4
HEADER HE13 RA 2X4 P




TE Part # 1-528015-6
PISTOL GRIP HANDLE



TE Part # 281740-4
HEADER HE13 STRAIGHT 2X4 P

Customers Also Bought




TE Part #1SNA115185R0500
M4/6.DE




TE Part #459722-3
BLADE SHEAR




TE Part #358733-000
CWT-3801



TE Part #925856-2
WIRE PIN 15.5-13.5 AWG .01 BR



TE Part #926933-2
WIRE PIN 18-17 AWG .01 BR



TE Part #1-1586019-0
10P RCPT VAL-U-LOK V0




TE Part #5053144070
RNF-100-3/8-0-SP



TE Part #34120
TERMINAL,SOLIS R 16-14 6



TE Part #323062
TERMINAL,SOLIS R HR 12-10 10



TE Part #1424650-1
BLADE, STRIP, OUTER

Documents

Product Drawings
PLUG HE13 IDC 180 2X4 P AWG 26-24
English

Product Specifications
Application Specification
English