

Product data sheet

Specifications



Straight length, Canalis KBA, 25 A, 1 circuit 3L+N+PE, 2 tap-off units, 2 m, white

KBA25ED4202W

Main

Range of product	Canalis
Product or component type	Busbar trunking
Product compatibility	KBA

Complementary

Device application	Lighting Power socket distribution
Maximum radiated magnetic field	2 pT
[Ue] rated operational voltage	230...400 V
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	25 A at 35 °C
Network frequency	50/60 Hz
[Icw] rated short-time withstand current	0.44 kA
[Ipk] rated peak withstand current	4.4 kA
Thermal stress limit	195 kA².s
THDI	0...15 % 25 A 15...33 % 20 A 33...100 % 16 A
Maximum voltage drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.54 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting mode	By clips
Busbar description	Straight length
Busbar trunking polarity	3L + N + PE
Number of circuits	1
Number of tap-off outlets	2
Control type	Without
Standards	EN/IEC 61439-6 EN/IEC 60439-2

Width	2140 mm
Depth	30 mm
Height	46 mm
Length	2 m
Colour	White (RAL 9003)
Net weight	1.9 kg
Quantity per set	Set of 6

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
IK degree of protection	IK06 conforming to EN/IEC 62262
Ambient air temperature for operation	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (93 % of In) 45...50 °C (89 % of In) 50...55 °C (85 % of In)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.0 kg
Package 1 Height	4.5 cm
Package 1 width	3.2 cm
Package 1 Length	214 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	144
Package 2 Weight	324.5 kg
Package 2 Height	52.8 cm
Package 2 width	64 cm
Package 2 Length	220 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	6
Package 3 Weight	13.0 kg
Package 3 Height	10.3 cm
Package 3 width	10 cm
Package 3 Length	219 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product
Contractual warranty	
Warranty	18 months

