



## TAHBE8040S-TAHBE8050S ERGO™ Insulated Slotted Screwdrivers with Kevlar String









### PRODUCT DETAILS

- For slotted head screws
- For work on live equipment up to 1000 V
- Phosphate finished tip
- Three-component handle developed according to the scientific ERGO™ process
- Soft material with ridged surface provides superior grip and greater force transmission
- Flat face to prevent rolling
- Colour-coded handle with the screw type symbol on the domed end
- High-performance alloy steel blade
- Standards: ISO 2380/DIN 5264, IEC 60900, VDE certified
- Suitable for working at height
- Permanent Kevlar textile wire loop maintains user ergonomics and full functionality
- Coloured tags with maximum weight for proper match with lanyard
- Compliant with DROPS best practices



### PRODUCT ATTRIBUTES

Product						
<b>TAHBE-8220S</b>	0.5 mm	100 mm	20 mm	122 mm	222 mm	40 g
<b>TAHBE-8040S</b>	0.8 mm	100 mm	20 mm	122 mm	222 mm	40 g
<b>TAHBE-8050S</b>	1.0 mm	125 mm	27 mm	122 mm	247 mm	70 g
<b>TAHBE-8255S</b>	1.2 mm	155 mm	36 mm	122 mm	272 mm	120 g

Follow the Fish!

