

Durable and breathable ESD safety overboots, designed with microporous laminate technology.

- **Certified performance:** AlphaTec® 2500 STANDARD Overboots ESD Bound - Model 407 is made of breathable fabric with the highest classifications for protection from biological agents, in accordance with EN 14126 for the penetration of blood, bodily fluids and blood-borne pathogens
- **Advanced defenses:** In addition, these chemical-resistant ESD overboots are produced with a unique material that delivers excellent strength and flexibility, as well as liquid and particulate protection
- **Reduced contamination risks:** These industrial overboots are also ideal for use in critical areas, as they are low lint, which reduces contamination risks



Industries

- Life Sciences
- Industrial
- Chemical
- Nuclear
- Law Enforcement


Applications

- Transferring liquids and solids
- Spill or leakage cleanup
- Maintenance
- Unexpected leakages spills or other releases
- Plant disinfection and sanitization
- Emergency Response
- Contaminated Environments


KEY FEATURES & BENEFITS

- **EN-certified protection from biohazards:** Reliable personal protection
- **Unique material:** Superior strength, optimal protection
- **Low linting:** Reduced risk of contamination in critical areas

Material Diagram



Seam Diagram



Performance Standards



EN ISO 13688:2013



Product Information

Product Information	
Available Sizes	42-46, 46-48
Color	White
Country Of Origin	China, Sri Lanka
Product Material	Microporous Polypropylene Laminate non-woven
Product Reference	2500 Overboots ESD - Model 407
Standards Overview	CE CATEGORY III (Type PB (6)-B, EN 14126)
Seam Type	Bound
Shelf Life	5 years
Style Number	W25B407

Suit components & accessories

Suit Components and Accessories	
Design Features	Overboots, elasticated opening, anti-slip sole, adjustable shoe tie, bound seams and ESD PVC sole.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

