



R-176

Insulated, waterproof impact gloves, with insulation and waterproof barrier to keep hands warm and dry



Impact



Cold

Abrasion Protection



Cut

Liquid Spray and Splash



Medium Duty

Insulated cut-resistant impact gloves, with a waterproof barrier to keep hands warm and dry

- **Specialized protection:** With a patented TPR (thermoplastic rubber) design, developed with F3 Technology™, RINGERS® R176 work gloves ensure knuckles and finger-length impact protection
- **Enhanced grip and cut resistance:** An additional palm layer, with grip-enhancing PVC patches, offers both advanced cut resistance and excellent grip
- **Added defenses:** Their proprietary waterproof barrier and 70g Thinsulate™ insulation guards against the elements, protecting hands while keeping them warm and dry
- **Enhanced features:** These RINGERS® gloves also feature an extended cuff with gaiter closure and increased visibility material with reflective cuff piping, for enhanced user safety, as well as touchscreen-compatible thumb tips, index and middle fingers



Industries

- Construction
- Oil and gas
- Chemical
- Automotive Aftermarket
- Mining

Applications

- Chaining up pipes
- Installation and dismantling of rigs
- Assembly of parts
- Assembly and disassembly of large pipes
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- General pumping work
- Handling iron
- Handling of tools
- Maintenance
- Operating of heavy machinery
- Cold Storage



R-176

Insulated, waterproof impact gloves,
with insulation and waterproof barrier
to keep hands warm and dry

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Additional palm layer with PVC patches:** Superb cut resistance and grip
- **Waterproof barrier and 70g Thinsulate™ insulation:** Warm, dry hands

Technologies



Touchscreen Compatible

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R176	Liner Material: HPPE Cuff Style: Extended cuff with gaiter closure		6, 8, 9, 10, 11, 12, 13	Black and Red	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

