

Han 16HPR EasyCon PE Modular Frame A-F



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 016 9933
Specification	Han 16HPR EasyCon PE Modular Frame A-F
HARTING eCatalogue	https://harting.com/09400169933

Identification

Category	Accessories
Series of hoods/housings	Han [®] HPR EasyCon
Type of accessory	Frame
Description of the accessory	for up to 6 single modules A ... F

Version

Size	16 B
Pack contents	1x male PE adapter 1x female PE adapter 2x M4/M5 distance bolts (AF 7) 2x M5/M6 distance bolts (AF 7) 2x M3 screw 2x M4 screw 2x washer SK S4

Technical characteristics

Conductor cross-section	4 ... 10 mm ² PE terminal power side 1 ... 2.5 mm ² PE terminal signal side
Tightening torque	0.5 Nm Fixing screws M3 1.5 Nm Fixing screws M4 6 Nm Distance bolt 0.8 Nm PE terminal clamp 1 ... 2.5 mm ² 1.5 Nm PE terminal clamp 4 ... 10 mm ²
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (accessories)	Zinc die-cast
	Stainless steel

Commercial data

Packaging size	1
Net weight	137 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194410
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466