

LED floodlight JARO 4060 P with Infrared motion detector 3450 lm, 30 W, IP65

For indoor and outdoor installation, IP 65.



Product number 1171250342
EAN 4007123684977

DESCRIPTION

- LED spotlight with super-bright Everlight SMD LEDs.
- Ideal for automatic illumination of entrance areas, driveways or carports as well as a deterrent against burglary and theft.
- Infrared motion detector can be continuously swivelled horizontally and vertically.
- Detection range up to 10 metres, detection angle approx. 180°.
- Switch-on time adjustable from approx. 10 seconds to approx. 5 minutes.
- With adjustable twilight sensor.
- User-friendly installation due to external, waterproof spring-loaded clamp.
- Front pane made of safety glass.
- Solid, modern aluminium housing.
- Adjustable mounting bracket.

TECHNICAL DATA

Luminous flux	3450 lm
Power consumption	30 W
Luminous efficacy	136 lm/W
Energy efficiency class	
Colour temperature	6500 K
Colour rendering index	80-89 (class 1B)
Min.-Max. Nominal input voltage	220 V - 240 V

With motion detector	Yes
Max. detection range	10 m
Min.-max. duty cycle	10 s - 5 min
With socket outlet	No
Impact strength	IK08
Protection class	I
Degree of protection (IP)	IP65
Basic colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.77 kg
Dimension LxWxH (without packing)	4.5 cm x 19.5 cm x 21.5 cm

Weight of product (including packaging)	0.88 kg
Dimension LxWxH (incl. packing)	6.2 cm x 19.5 cm x 22 cm

SCOPE OF DELIVERY

LED floodlight JARO 4060 P with infrared motion detector