

AutoMax™

AutoMax™ 100M Mini-Cut (P-4) Auto Feed Shredder – SilentShred™

Home Office / Deskside (1 Users)

Features:


- 100-sheet auto feed and 10-sheet manual feed shredding capacity (70gsm paper)
- 4x10mm Mini-Cut (Security Level P-4) - Shreds each A4 sheet into over 1000 particles. Around 4x more secure than standard cross-cut
- Shreds non-stop for up to 15 minutes. Ideal for regular use
- Auto Reverse, SilentShred and Sleep Mode features ensure safe, disruption-free shredding
- Large, 23 litre pull-out bin and extra-small particle size give a capacity of at least 175 sheets
- Accepts staples, credit cards and paper clips through the manual feed slot
- Up to 3 Years Warranty – Register for extra year (2+1)



Up to 3 year (2+1 year)
machine warranty after
product registration
on Fellowes.com



Specifications

Sheet capacity	100 (10 manual)
Bin Capacity	23L (Pull-out Bin) (515 sheets)
Cut-type	Mini-cut (4x10mm)
Security Level	P-4 (1559 particles per A4 sheet)
Feed Type	Hybrid
Runtime (minutes)	15 on / 35 off
Throat width (mm)	220 mm
Also shreds	 (manual slot only)
Colour	Black
Product Dimensions (H x W x D) / mm	673 x 384 x 365
Product Weight	13.2 kg
Retail Packaging Dimensions (H x W x D) / mm	687 x 380 x 450
Retail Packaging Weight	14.1 kg
Outer Carton Dimensions (H x W x D) / mm	707 x 393 x 463
Outer Carton Weight	17.3 kg
Quantity per Outer Carton	1
Country of Origin	China
Warranty	3-year machine (2 + 1) / 5-year cutters



Code (EU)	4629201	UPC: 043859741854	SCS: 50043859741859
Code (UK)	4629301	UPC: 043859741861	SCS: 50043859741866
Code (CH)	4614801	UPC: 043859743117	SCS: 50043859743112

Recommended

Oil 355ml	3608601
Oil 120ml	3608501
Oil Sheets	4025601