General Purpose Enclosures



Features

- Wide temperature range -60°C to +200°C
- Watertight solution for outdoor and indoor application
- For use in aggressive atmospheres and hygienic environments
- Enclosure base with four mounting holes
- Two retaining brackets and welding studs for mounting built-in components
- Four possible grounding points on the retaining brackets

RS PRO Stainless Steel Enclosure, hinged lid, 200x200x80mm

RS Stock No.: 213-4045



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

General Purpose Enclosures



Product Description

The stainless steel enclosures are particularly suitable for use in aggressive atmospheres and hygienic environments. The construction of the enclosure and the surface finish also allow for optimal cleaning. The IP66 protection class makes the enclosure waterproof and reliably protects the built-in components from dust. Thus, the stainless steel enclosures are suitable for indoor and outdoor use. The closure of the enclosure and the connection between cover and base are fixed with robust screws. In addition, mounting plates and mounting rails offer the possibility of integrating built-in components in the enclosure.

General Specifications

Use	General Purpose Enclosures				
Body Material	Stainless Steel 304				
Colour	Grinded, grain 320				
Lid Colour	Grinded, grain 320				
Handheld	No				
Flanged	No				
Shielded	No				
Number of Knockouts	0				
Transparent Door	No				
Explosion Proof	No				
Features	Hinged Lid, Chemical Resistant				
Cover Screws Material	Stainless Steel				
Temperature Range (Continuous)	-60 - +200°C				

General Purpose Enclosures



Mechanical Specifications

Gasket Material	Silicone			
External Height	200 mm			
External Length	200 mm			
External Width	80 mm			
External Dimension	200 mm x 200 mm x 80 mm			
Weight	1,78 kg			
Thickness	1.25 mm			

Protection Category

IP Rating	IP66
IK Rating	IK09

Additional Information

EAN	4057624085032
Approvals	On demand

Similar Products

Stock No.	Brand	Product Name	Body Material	Colour	Shielded
213-4044	RS PRO	RS PRO Stainless Steel Enclosure, screwed lid, 200x200x80m	Stainless Steel	Grinded, grain 320	No
213-4047	RS PRO	RS PRO Stainless Steel Enclosure, hinged lid, 300x200x80m	Stainless Steel	Grinded, grain 320	No

m