

J-S.208A - Click wrenches with removable ratchet



Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Accuracy: $\pm 4\%$.
- Reliability of mechanism 25 000 cycles.
- End fitting: 9 x 12 or 14 x 18 mm for accessories (ratchets, polygon and open end bits).
- One-way wrenches usable for unscrewing by reversing the bits.
- Sensitive and sound click when reaching torque.
- Automatic reset.
- Supplied with ISO 6789 calibration certificate.
- Supplied in plastic protection tube with ratchet.

	Length L [mm]	Attachement [""]	Capacity [Nm]	Graduation [Nm]	Weight [Kg]	Ratchet [""]	Square [in]	Contents []
J.208A50	337.0	9 x 12	10 - 50	0.5	0.78	J.372V	3/8	
S.208A100	396.0	9 x 12	20 - 100	1.0	0.92	S.372V	1/2	Case: CKS.67SJ 1
S.208A200	466.0	14 x 18	40 - 200	2.0	1.1	S.382V	1/2	Roll: N.38A-9E
S.208A340	618.0	14 x 18	40 - 200	2.0	1.1	S.382V	1/2	Box BP.39VA + Tray PL.206