



050996-1-100

R2G4, 4.0mm2, RED SPOOL B4, 100V, PVC, 100C



Product Properties:

Number of cores	1 .
Flame retardant	According to IEC/EN 60332-1-2
Permitted cable outer temperature after assembling without vibration	-40-100 °C
Max. conductor temperature	100 °C
Single insulated/Double insulated	Single insulated
Min. permitted bending radius, stationary application/permanent installation	18 mm

Dimensions:

Nominal cross section conductor	4 mm ²
MOQ	100 .
Outer diameter approx.	3.6 mm
Min. permitted bending radius, stationary application/permanent installation	18 mm
Diameter conductor	4 mm
Unit	m

Approvals:

Approved according to Volvo R2 7613, 111/3	Yes
Flame retardant	According to IEC/EN 60332-1-2
Approved according to CE	Yes

Compliance:

CA Proposition 65	No CA Prop65
-------------------	--------------

Conflict Minerals	N/A, Contains no conflict minerals
Extended Minerals	N/A, contains no extended minerals
PFAS	No PFAS
POPs	No POPs
REACH	No SVHC (240 Subs. 23 Jan 2024)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC003248 - Power cable < 1 kV, for permanent installation
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	R2G4, Single Conductor, Red copper
Alternative SKU	050996-1-100

Logistic information:

Barcode	733117640500
Country of origin	SE
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	050996-1-100
Taric code	85444995
Unit	m

*We reserve the right to make technical changes and disclaim any typographical errors.