

Endress+Hauser Capacitance level switch FTW325-72B1A

Point level switch with intrinsically safe signal circuit for connection to a conductive sensor.



Picture for reference only. Product appearance may vary based on configuration

The Nivotester FTW325 is a point level switch with intrinsically safe signal circuit for connection to a conductive sensor. It has a compact housing for easy series mounting on a standard DIN rail in the cabinet.

- Cable monitoring up to sensor
- Compact housing for easy series mounting on standard DIN rail in the cabinet
- Adjustable sensitivity range

Configuration of FTW325-72B1A:

Approval:	7	Non-hazardous area + EAC marking
Housing:	2	Rail mounting, 22.5mm, 2-channel
Power Supply:	B	20-30VAC/20-60VDC
Switch Output:	1	1x SPDT level + 1x SPST alarm
Additional Option:	A	Basic version

Alternative part number: FTW325-72B1A