

Hot air tool - Professional Line

HM 2320 E

Case
EAN 4007841 089672
Article number 089672



series 5



Timer function

2300 W

2300 W Output

Display

Display (LCD)



80 - 650°C



stepless adjustable



150 - 500 l/min.



Suitable for
pluggable nozzles



VDE



CE

Function description

Powerhouse of energy saving. Sustainable working for the professional tradesman or industry. The 2300 W HeatMatic 2320 E provides absolute safety even with sensitive materials thanks to the display and the precise temperature setting of 80-650°C.

Technical specifications

Temperature	80 – 650 °C	Restart protection	Yes
Airflow rate	150 – 500 l/min	Temperature scanner	Yes
Temperature setting	in 10°C steps by joystick	Thermal cut-out	Yes
Settings made via	joystick	Thermostat	Yes
Temperature display	LCD display	Nozzle receiver, type	34
Airflow control	Settings	Cord length	3 m
Programming function	Yes	Dimensions (L x W x H)	253 x 87 x 200 mm
Loc function	Yes	PU1, net weight	1,08 kg
Residual heat indicator	Yes	Manufacturer's Warranty	1 year
Cool function	No	PU1, EAN	4007841089672
Motor, type	Brush motor	Scope of delivery	incl. reflector nozzle, wide jet nozzle 50mm, reducing nozzle 9mm, shrink hose 1.6-9.5
Heating element	Ceramic heating element	Output	2300 W
Mains power supply	220 – 230 V / 50 – 60 Hz	Product category	Hot air tool
Function, hanger	Yes		

Accessories

EAN 4007841 014919

Temperature scanner HL Scan

<https://www.steinel.de>

Subject to technical modifications

03.2025 Page 1 from 2

HM 2320 E

Case
EAN 4007841 089672
Article number 089672



Accessories

EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E
EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 009571	Reduction nozzle
EAN 4007841 070618	Reduction nozzle
EAN 4007841 070717	Reduction nozzle
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 068035	Adapter nozzle
EAN 4007841 070311	Window nozzle
EAN 4007841 070410	Window nozzle
EAN 4007841 070113	Surface nozzle
EAN 4007841 070212	Surface nozzle
EAN 4007841 070519	Reflector nozzle
EAN 4007841 070915	Welding nozzle
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 087715	Flat angled nozzle 40x2 mm for discharge pipe bead
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E