



Fuse base, low voltage, 32 A, AC 550 V, BS88/F1, 1P, BS, front connected, back stud connected

Part no. 32A 550V F/HOLDER 10 1.3KG
Catalog No. 32NNSFBS

Delivery program

| | | | |
|------------------------------|---|---|----------------------------------------|
| Product range | | | Fuse accessory |
| Basic function | | | Fuse-holder |
| Field of application | | | low voltage |
| Rated current | I | A | 32 |
| Rated voltage | | | AC 550 V |
| Construction size | | | BS88/F1 |
| Description | | | front connected back stud connected |
| Number of poles | | | 1P |
| usable for size/applications | | | fuse-link NSD |
| Standard/Approval | | | BS |

Technical data ETIM 7.0

| | | | |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---|-------|
| Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067) | | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecl@ss10.0.1-27-14-21-06 [AKE278013]) | | | |
| Construction size | | | Other |
| Number of poles | | | 1 |
| Rated current | | A | 32 |
| Bus-mounting type | | | Yes |
| Swivelling mechanism | | | No |

Additional product information (links)

| | |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product datasheet (pdf) | http://www1.cooperbusmann.com/bussmanncms/uploads/Fuseholder_brochure_lowres(1).pdf |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|