

FEATURES

- Mancooler fan 300mm
- Material die casting aluminum alloy housing
- Wire guard for safety
- Portable

RS PRO Floor, Heavy Duty Fan 3900m³/h 300mm blade diameter 1 speed 220 → 240 V with plug: Type G - British 3-pin

RS Stock No.: 810-1148



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO wheel mounted fan designed for cooling and air circulation in commercial, industrial, retail or leisure applications. A Mancooler is a type of heavy duty axial fan which are extremely powerful and give off air streams over a longer distance. This fan can operate on the floor as a free-standing unit and the wheels make it portable and easy to move.

This mancooler fan is available with either UK or Euro plug.

[810-1148](#) – UK plug

[810-1145](#) – Euro plug

General Specifications

Fan Type	Floor
Air Flow	3900m³/h
Blade Span	300mm
Number of Speeds	1
Material	die casting alum alloy housing
Finish	red powder coating
Adjustable Stand	No
Non-Slip Base	No
Applications	Industrial, Factory shop floors, Cold storages, Rubber processing plants, Retail, Leisure

Electrical Specifications

Power Source	Mains powered
Supply Voltage	220V-240V
Plug Type	Type G - British 3-pin
Power Consumption	550W
Speed	2800rpm /3300rpm
Noise Level	89dB
VDE Power Cord	Yes

Mechanical Specifications

Volume Capacity	
-----------------	--

65 / 77 M3/min
