

Eaton 248348

Catalog Number: 248348

Eaton Distribution parts. Two way switchp22 CO, 16A, 230 V, 20kA, DAY-0-NIGHT

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248348
EAN	Product Length/Depth
4015082483487	80 mm
Product Height	Product Width
75 mm	17.5 mm
Product Weight	Compliances
0.079 kg	RoHS conform

Product specifications

Rated operational voltage (Ue) - max

240 V

Voltage rating - min

0 V

Width in number of modular spacings

2

Number of poles

Two-pole

Color calotte

Other

Switch type

Two-way switch

Rated short-time withstand current (Icw)

10 kA

Lamp socket

Other

Built-in depth

80 mm

Amperage rating

20 A

Voltage type

AC

Lamp type

Other

Degree of protection

IP40

Lamp power

0 W

Number of contacts (change-over contacts)

2

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Inscription

Resources

Declarations of conformity

[DA-DC-03_Z-S_SC_SB](#)

[DA-DC-03_Z-S](#)

Drawings

[eaton-dimensions-mas-z-s.jpg](#)

Wiring diagrams

[Z_S_2W](#)

Other

Rated operational current for specified heat dissipation (In)

20 A

Rated Switching Capacity

0.02 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia