



## Main

Range	Thalassa
Product name	Thalassa PLS
Device short name	PLS
Device application	Multi-purpose
Product or component type	Insulating modular box
Enclosure nominal height	180 Mm
Enclosure nominal width	270 Mm
Enclosure nominal depth	180 Mm
Enclosure mounting	Wall mounted
Device composition	1 cover: on enclosure 1 rear part: on enclosure locking screws
Body type	One piece moulded
Type of front cover	Low transparent cover
Lock type	Slot screw

## Complementary

Removable parts	Cover locking screw
Material	Cover: polycarbonate Rear: polyester reinforced with fibreglass
Colour	Body: grey (RAL 7035)
Standards	NEMA classification 13 IEC 62208 NEMA 4X
Product certifications	UL

## Environment

Electrical insulation class	Class II
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 62262
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-30...70 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.375 Kg
Package 1 Height	20 Cm
Package 1 width	29 Cm
Package 1 Length	20 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**