

TVIP10005A

VGA Network Compact Camera

This camera takes real-time images in VGA resolution and transmits them via the IP network. A web browser (ABUS DDNS Server) or a free app can be used to operate the camera and access live images. Since the camera requires hardly any networking knowledge, it is ideal for over-the-counter sales.

Video surveillance for your home

Simply see who is coming or who is at the door – without extras, without elaborate configuration. That's what this VGA LAN compact camera is made for. It is thus ideal for basic surveillance with real-time images, which is often sufficient for private use.

Reduced to the essentials

“Less is more” – this is the concept behind the VGA camera. The advantage: The LAN camera can be easily installed and operated by anyone, even if they have no IP networking knowledge. Setup of the camera parameters through the ABUS DDNS Server is as good as automatic; all you need to do is connect the camera with the router using a network cable. This means you don't need to take note of and find out IP addresses.

Flexible mounting

The camera is suitable for mounting on all surfaces – on the wall or on the base included in the scope of delivery, for example.

Enhanced functional scope

If recording is to be set up, the use of NAS (Network Attached Storage) is recommended. You can use advanced security functions in



Product highlights:

- LAN camera for simple indoor surveillance tasks
- Simple initial operation using ABUS DDNS server
- Uncomplicated live cast and playback via app
- VGA resolution: 640 x 480 @ 25 fps
- Starter camera that can be used without IP networking familiarity
- Optimal price/performance ratio

Your Partner:
ABUS-TEST
Linker Kreuthweg 5
86444 Affing
+49 (8207) 959900

TVIP10005A

VGA Network Compact Camera

conjunction with the ABUS VMS software for video management. This is included in the scope of delivery at no cost.

Note: The product with the English language package is TVIP10005B

Your Partner:
ABUS-TEST
Linker Kreuthweg 5
86444 Affing
+49 (8207) 959900

TVIP10005A

VGA Network Compact Camera

Technical Data

| | |
|---------------------------------|--|
| Sensor | 1/4" Progressive Scan CMOS-Sensor |
| Camera type | Color |
| Resolution | 640 x 480, 320 x 240, 160 x 120 |
| Image elements (total) | 640 x 480 |
| Image elements (effective) | 640 x 480 |
| Horizontal angle of view | 67 |
| Digital zoom | 10 |
| Minimum illumination (color) | 0,8 lux |
| Frames per second | 25 |
| Number of parallel streams | 1 |
| White balance | AWB |
| Backlight compensation | BLC |
| Mikrophone | Ja |
| Network connection | RJ45 LAN |
| Network protocol | TCP/IP, DHCP, PPPoE, ARP, ICMP, DNS, NTP, UPnP, HTTP, UDP |
| Power supply | 5 DC |
| Power consumption | 260 V |
| Protection | IP34 |
| Dimensions (wxhxd) | 63,1 x 77,1 x 32,4 |
| Certificate | CE, RoHS, Reach |

Your Partner:
ABUS-TEST
 Linker Kreuthweg 5
 86444 Affing
 +49 (8207) 959900