



ENGLISH

Datasheet

RS Pro SR57 1.55V Silver Oxide Coin Button Battery

RS Stock No: **494-2403**



Product Details

RS Pro SR57 silver oxide coin button battery is non-rechargeable cell, suitable for use in cameras, clocks, watches and calculators. It features superior discharge characteristics in comparison to alkaline cell and nominal voltage of 1.55 V. This battery is shock, vibration and acceleration resistant.

Features and Benefits

- Superior discharge characteristics in comparison to alkaline cells
- Good low temperature performance characteristics
- Good resistance to shock, vibration and acceleration
- Low constant internal resistance
- Excellent service maintenance
- Nominal voltage 1.55 V

**Specifications:**

Also Known As	395, SR926SW, SR927, SB-AP/DP, 280-48, LA, V395, D395, 610, S926E
Brand Range	RS
Chemistry	Silver Oxide
Size	SR57
Terminal Type	Standard
Capacity	55 mAh
Diameter	9.5 mm
Dimensions	9.5 x 2.7 mm
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.55 V
Operating Temperature Range	-10 to +50°C
Size	SR57
Weight	0.8 g
Typical Application	Cameras, Clocks, Watches, Calculators