

Datasheet

AVM-01/AVM-03 Anemometer

FEATURES:

- Sensitive for low/high air velocity
- Ergonomic Design
- 0.3~45m/s range



SPECIFICATION:

-	Measurement	Range	Resolution	Accuracy
Air Velocity	M/S	0.3-45.0	0.1	+/- 3% or 0.1
	KNOTS	0.6-88.0	0.1	+/- 3% or 0.1
	ft/min	60-8800	10	+/- 3% or 10
	Km/hr	1-140.0	0.1	+/- 3% or 0.1
Optional Range	MPH	0.7-100.0	0.1	+/- 3% or 0.1
Temperature AVM-03	°C	0-60	0.1	+/- 0.8
Temperature AVM-03	°F	32-140	0.1	+/- 1.5

Operating Temperature	10°C-50°C
Operating Pressure	500mB-2bar
Display	Large 3 1/2 digit LCD
Power Source	1pc of 9V Battery
Dimension	168mm x 90mm x 31.3mm
Weight	500g
Accessory	Carrying Case, 9V Battery, Instruction Manual