

894 90

Single open ended spanner

metric

Code	ETIM
6578080	EC002130
EAN	UNSPSC
4010886657805	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-01
Customs tariff number	
82041100	



Article description

- Acc. to DIN 894, ISO 3318
- Manganese phosphate finish up to 38 mm, steel-grey up from 41 mm
- Size 10 - 135 mm with angling hole
- Carefully forged and professionally machined:
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Jaw set at 15°
- Secure grip thanks to profile shaft - very ergonomic and handy
- Overloading indicated by deformation
- * not standardised

Article information

Contents (Qty of pieces)	1	Standard	not standardised
Net weight [kg]	3,72 kg	Width across flats l [mm]	90
Total length [mm]	685 mm	Head height l [mm]	23 mm
Total width [mm]	172 mm	Width of head l [mm]	173,0 mm
Total height [mm]	23 mm	Jaw set	15°
Surface	steel-grey	Ratchet function	no
Material	Vanadium steel 31CrV3		