

PRODUCT-DETAILS

# TC5345A

## 4WAY MTG BASE 1.1X1.1IN NAT NYL ADH



### General Information

Extended Product Type	TC5345A
Product ID	7TAG009800R0002
EAN	5414363058946
Catalog Description	4WAY MTG BASE 1.1X1.1IN NAT NYL ADH
Long Description	Four-Way Adhesive Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.7mm (0.22 Inches), Self-Adhesive Mounting Method, 100 Pack

### Ordering

EAN	5414363058946
UPC	786210872247

### Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	6 in 152 mm
Package Level 1 Depth / Length	12 in 305 mm
Package Level 2 Units	500 piece
Package Level 2 Width	6.6 in 168 mm
Package Level 2 Height	7.9 in 201 mm

Package Level 2 Depth /  
Length

9.7 in  
246 mm

## Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19740913
Material	Nylon/Polyamide 6.6
Mounting Holes	#6
Mounting Type	Self-Adhesive
Number of Batteries	0
Number of Entrances	4
Process Temperature Rating	-32 to +150 °F
Product Name	NYLON MOUNTING BASE FOR CABLE TIE
Product Type	Mounting Base
Special Functions	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5345A
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC5345A
REACH Declaration	9AKK107992A3999
RoHS Information	9AKK107991A8070

## Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

