



GFK Floor Checkweighing Scales

The GFK offers all the features needed for weighing, check weighing with LED limit indicators and parts counting application with fully selectable sample or unit weight. Built tough for a variety of industries the GFK can meet the demands of warehouse, production floor or even medical applications.

Check weighing applications are trouble free with amber, green and red indicators to show the operator if the item is under, over or at the preset limits. A stainless steel top pan offers ample weighing surface and a standard pillar allows for easy mounting of the indicator if desired. The GFK includes a RS-232 interface with date and time, bright backlit display with capacity tracker, a built-in rechargeable battery and external power supply.

With over three decades of experience in the production of weighing equipment you can trust Adam for quality products that offer a range of features designed for a many different applications.



GFK Floor Checkweighing Scales

Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to "always on", "always off" or "light only when weighing"
- Capacity tracker built into display for easily monitoring possible overloads
- Checkweighing LEDs light to clearly show under, over and acceptable limits
- Adjustable leveling feet help optimise setup
- Colour-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows easy cleaning
- RS-232 interface for connection to computers and printers
- Sealed keypad protects against dirt and accidental spills
- Audible overload alarm warns when capacity has been exceeded
- Checkweighing with audible alarm

- Hold function freezes the displayed weight, allowing time to lapse without losing the result
- Parts counting with freely selectable sample sizes
- Parts counting optimisation automatically refines piece weight as parts are added
- Preset tare function speeds the process of repetitive weighing
- Programmable for counting to a preset number of parts
- Selectable digital filtering for animal/dynamic weighing delivers stable results for moving subjects
- Selectable digital filtering helps minimise effects of vibration and disturbances
- Zero-tracking feature ensures display returns to zero reading
- Rechargeable battery included for operation virtually anywhere
- Programmable auto power-off to save energy

Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Checkcounting
- Dynamic / animal weighing

Model	GFK 75	GFK 75H	GFK 150	GFK 150H	GFK 300	GFK 600	GFK 60M	GFK 150M	GFK 300M
Capacity	75kg	75kg	150kg	150kg	300kg	600kg	60kg	150kg	300kg
Readability	5g	1g	0.01kg	2g	0.02kg	0.05kg	0.02kg	0.05kg	0.1kg
Repeatability (S.D.)	5g	2g	10g	4g	20g	50g	40g	100g	200g
Linearity (+/-)	10g	3g	20g	6g	40g	100g	40g	100g	200g
Pan Size	400x500mm					600x800mm	400x500mm		
Weighing Units	g, kg						kg		
Stabilisation Time (sec)	2								
Interface	RS-232								
Calibration	External calibration								
Display	Backlit LCD with 20mm-high digits								
Power Supply	Mains power cord / Internal rechargeable battery								
Operating Temperature	-10° to 40°C								
Housing	ABS								
Overall Dim.	400x620x860mm					600x940x-900mm	400x620x860mm		
Net Weight	12.30kg					25.50kg	12.30kg		
Approvals	N/A						NRCS approved / National Measurement Institute		

With more than forty years of experience in the production of balances and scales, professionals worldwide rely on Adam for feature-rich, quality products with best-in-class value - The right balance of speed, performance and value.

Supplied by:

Item number

- 3052010526
- 3126011263
- 3126011281
- 1120011156
- 3074010266
- 3074010507
- 600002028

Description

In-use cover
 Thermal paper for item no. 1120011156-ATP printer
 Thermal paper for item no. 1120011156-ATP printer (pack of 10)
 ATP Adam thermal printer
 RS-232 cable (null-modem)
 RS-232 to USB Adapter
 (must order corresponding RS-232 cable)
 Adam DU Software