

Part Number : [190720048](#)
Product Description : VibraKrimp Ring Tongue
Terminal 16-14 AWG for Stud Size 3/8" (M9), Length
31.27mm
Series Number : 19072
Status : Obsolete
Product Category : Ring and Spade Terminals
Engineering Number : BB-418-38



Documents & Resources

Drawings

[190720048 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Ring and Spade Terminals
Series	19072
Description	VibraKrimp Ring Tongue Terminal 16-14 AWG for Stud Size 3/8" (M9), Length 31.27mm
Keyword	Ring Terminal, Ring Terminals
Product Name	VibraKrimp
Type	Ring
UPC	800753073913

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.301/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm

Stud Size	2 (M2)
Wire Size (AWG)	14, 16

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Crimp Hand Tool	<u>640016800</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640056800</u>