

## **1 Port USB Wireless-N 150Mbps AirPrint™ Server - 802.11b/g/n**

*StarTech ID: PM1115UA*



The PM1115UA Wireless-N USB AirPrint Server lets you print directly from your iPhone, iPod touch or iPad devices to a standard USB printer over a wireless network.

With this compact AirPrint server connected to your existing wireless network, it enables iOS® / iPad printing direct from the print menu of your device, without the hassle of transferring your documents or photos to another system.

You can also use the AirPrint server with other laptop and desktop systems on your network, effectively turning any standard USB printer into a fully networked printer. This compact server supports 802.11b/g/n standards and features an easy-to-use web interface as well as print management software for Windows® and Mac OS®. For added flexibility, up to 2 printers can be connected to the print server using a USB hub (not included).

As an added benefit, using a wireless print server makes your printer available from anywhere within range of your wireless router, so you can place it in a convenient location without being tied down by a network cable.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Applications**

- Print directly from your iOS-based devices over the wireless network
- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- Place your printer in a convenient, central location without requiring a network cable

## Features

- Supports Apple AirPrint on iPad (all models), iPhone (3GS or later) and iPod touch (3rd generation or later)
- Also supports network print sharing with desktop and laptop systems
- Compliant with 802.11b/g/n wireless networks, with data rates up to 150 Mbps
- USB 2.0 support
- Optional 10/100 Mbps RJ45 LAN Port
- Compact footprint
- Easy-to-use web interface and included software for configuration on Windows or Mac OS

Technical Specifications

|                            |   |
|----------------------------|---|
| Warranty                   | 2 Years   |
| Color                      | Black   |
| Enclosure Type             | Plastic   |
| Product Height             | 24 mm [0.9 in]  |
| Product Length             | 85 mm [3.3 in]  |
| Product Weight             | 56 g [2 oz]   |
| Product Width              | 57 mm [2.2 in]  |
| Industry Standards         | IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE 802.11b/g/n Wireless   |
| Interface                  | USB 2.0   |
| Interface                  | RJ45 (10/100 Ethernet)  |
| Interface                  | Wireless Ethernet   |
| Ports                      | 1   |
| Frequency                  | 2.4 GHz   |
| Maximum Data Transfer Rate | 150 Mbps  |
| Security Features          | WEP Data Encryption   |
| Security Features          | WPA Data Encryption   |
| Security Features          | TKIP/AES  |
| Supported Protocols        | TCP/IP  |
| Connector Type(s)          | 1 - USB A (4 pin) Female  |
| Connector Type(s)          | 1 - RJ-45 Female  |
| Connector Type(s)          | 1 - Wireless N (IEEE 802.11n)   |
| OS Compatibility           | Windows® 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64)<br>Windows Server® 2012, 2008 R2, 2003(32/64)<br>Mac OS® 10.8 and up (Tested up to 10.9) |
| <b>Note</b>                | AirPrint is an Apple® technology that is supported on the iPad (all models), iPhone (3GS or later) and iPod touch (3rd generation or later)                       |
| <b>Note</b>                | OS Compatibility refers to the included software only – the Print Server itself can be used without software on any platform that supports network printing       |
| LED Indicators             | 1 - Power   |

|                           |   |
|---------------------------|---|
| LED Indicators            | 1 - WLAN                                |
| LED Indicators            | 1 - LAN                                 |
| LED Indicators            | 1 - USB                                 |
| Center Tip Polarity       | Positive                                |
| Input Current             | 0.2 A                                   |
| Input Voltage             | 100 ~ 240 AC                            |
| Output Current            | 1 A                                     |
| Output Voltage            | 5 DC                                    |
| Plug Type                 | M                                       |
| Power Source              | AC Adapter Included                     |
| Humidity                  | 0~70% RH                                |
| Operating Temperature     | 0°C to 40°C (32°F to 104°F)             |
| Storage Temperature       | -10°C to 60°C (14°F to 140°F)           |
| Shipping (Package) Weight | 324 g [11.4 oz]                         |
| Included in Package       | 1 - Wireless-N USB 2.0 AirPrint™ Server |
| Included in Package       | 1 - Universal Power Adapter (NA/UK/EU)  |
| Included in Package       | 1 - Driver CD                           |
| Included in Package       | 1 - Instruction Manual                  |

Certifications, Reports and Compatibility

