

Eaton 12TXLEJ200

Catalog Number: 12TXLEJ200

Eaton Bussmann series medium voltage DIN fuse, 200 A, AC 12 kV, 3.5", 88 x 292 mm, backup, DIN, with striker

General specifications



Product Name

Eaton Bussmann series medium voltage
DIN fuse

Catalog Number

12TXLEJ200

EAN
5027590225786

UPC

051712186162

Product Length/Depth

360 mm

Product Height

88 mm

Product Width

88 mm

Product Weight

3700 g

Compliances

DIN 43625
VDE 0670-4
IEC 60282-1

Certifications

UL
VDE

Product specifications

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

200 A

Fuse indicator

With Striker

Fuse size

88 x 292 mm

Breaking capacity

63 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

Yes

Resources

Technical data sheets

[720106 24kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I2T)

1.5 x 105

Resistance

3.8 Ohms

Watt losses

333 W

Fuse diameter

88 mm

Color

Brown

Interrupt rating

63 kAIC

Construction size

88 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

12 kV

Fuse type

TXLEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia