

Features

- 5 mm pitch
- Voltage Rating: 300V
- Current Rating: 16A
- Low Mating Force
- 2 WAY VERTICAL STD PCB SCREW TERMINAL

RS PRO 5MM PITCH 2 WAY VERTICAL STD PCB SCREW TERMINAL

RS Stock No.: 0631128



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- A series of RS Pro vertical mount screw terminals. Available from 2 way to 5 way, these PCB terminal blocks allow a perfect connection with your wiring application. All models are highly reliable and excellent quality..
- Tin plated brass
- Standard accepts wire 22-14AWG 2.5 mm²
- Tin plated brass terminals in glass filled PBT bodies

General Specifications

Number of Contacts	2
Number of Rows	1
Pitch	5mm
Mounting Type	Through Hole
Type	PCB Terminal Block
Body Orientation	Straight
Number of P	2
Gender	Male
Termination Method	Screw (M3, Steel(A3), Zinc Plated
Torque	0.5N.m
Wire Protector	Stainless steel
Contact Material	Brass
Contact Plating	Tin plated
Housing	PBT(UL94V-0)
Colour	Dark grey

Electrical Specifications

Voltage Rating	300V
Current Rating	16A

Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	5.0 mm
Pin size	1.0mm
Pin height	4.2mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, VDE, CE
Declarations	Reach

Spec Drawings



