



### Main

Range of product	Canalis
Product name	KS
Product or component type	Feed unit
BAR MATERIAL	Aluminium
Product compatibility	FL21 gland plate
[Ie] rated operational current	800 A 1000 A
Mounting location	Left
Colour	White (RAL 9001)

### Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...690 V
Connections - terminals	Lug for 240 mm <sup>2</sup> flexible Lug for 300 mm <sup>2</sup> rigid
Control type	Without
Number of circuits	1
Provided equipment	End cover
Mounting mode	By screws
Mounting support	Busbar
Standards	IEC 61439-6 IEC 60439-2
Width	753 mm
Depth	370 mm
Height	500 mm
Body material	Metal
Net weight	24.5 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------

