

Specifications

Eaton 5.5ABWNA5E



Eaton Bussmann series medium auxiliary fuse, VT fuse-link, medium voltage, 5 A, AC 5.5 kV, 142 x 25.4 mm, back-up, BS, IEC, US, 5E, Protect of auxiliary trans, 5 A, 5E, 50K A Breaking Cap, Inst Air, E, British Standard, AC, Class back-up



General specifications

PRODUCT NAME	Eaton Bussmann series medium auxiliary fuse
CATALOG NUMBER	5.5ABWNA5E
EAN	5027590048422
UPC	051712835893
PRODUCT LENGTH/DEPTH	142 mm
PRODUCT HEIGHT	25.4 mm
PRODUCT WIDTH	25.4 mm
PRODUCT WEIGHT	194 g
CERTIFICATIONS	IEC60282-1

Product specifications

AMPERAGE RATING	5 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	142 x 25.4 mm
RESPONSE TIME	5E
BREAKING CAPACITY	50 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Auxiliary transformer protection
RELEASE CHARACTERISTIC	E
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	No
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical
FUSE DIAMETER	25.4 mm
RESISTANCE	0.2 ohms
INTERRUPT RATING	50 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	142 x 25.4 mm
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	5.5 kV
TYPE	fuse
SPECIAL FEATURES	Non-Indicating
APPLICATION	Protection of auxiliary transformers
FUSE TYPE	ABWN

Resources

BROCHURES

[eaton-bussmann-circuit-protection-brochures-en.pdf](#)

[eaton-bussmann-series-product-range-overview-brochure-br134002en-en-us.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

