

Technical data sheet

Article number:
924-00558

2HB3

Product Group	Lip Blade Terminals
Product Family	Single Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	4.7 mm
Length (L)	28.3 mm
Length (L2)	10.7 mm
Length (L3)	17.6 mm
Max Current	27 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	2.8 mm
Width (W3)	2.2 mm

RoHS 