

A674 - CS Cut F13 Leather Glove

Collection: Cut Resistant

Range: Hand Protection

Materials: HPPE, Glass Fibre, Nylon, Elastic, Steel Fibre, Cow Split Leather

Dipping:

Inner Pack: 12

Outer Carton: 72

Product information

CS cut resistant gloves provide cut level F protection. Leather palm makes this glove ideal for glass handling and working with hot items up to 100°C for short periods. 13-gauge liner ensures an excellent fit. Reflective label increases glove visibility in low light conditions.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 4

EN 388: 2016 + A1: 2018 (4X44F)

EN 407: 2020 (X1XXXX)

ANSI/ISEA 105: 2016 CUT Level (A7)

ANSI/ISEA 105: 2016 ABRASION Level (6)

ANSI/ISEA 105: 2016 PUNCTURE Level (4)



Features

- Level F cut resistance
- Leather palm greatly improves durability
- Additional reinforced protection on palm and forefinger areas
- Designed for tasks that require reinforced abrasion resistance
- Protection against contact heat up to 100°C
- Reflective label for improved visibility
- 13 gauge liner constructed for durability and precise fitting
- CE certified
- Retail tag which aids presentation for retail sales
- UKCA marked



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A674 - CS Cut F13 Leather Glove

Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/20728-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: AB0321/21221-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A674K8RXS	Black	56.0	42.0	40.0	0.1220	0.0941	5036108366552	25036108855708
A674K8RS	Black	56.0	42.0	40.0	0.1270	0.0941	5036108366538	25036108855685
A674K8RM	Black	56.0	42.0	40.0	0.1360	0.0941	5036108366521	25036108855678
A674K8RL	Black	56.0	42.0	40.0	0.1450	0.0941	5036108366514	25036108855661
A674K8RXL	Black	56.0	42.0	40.0	0.1560	0.0941	5036108366545	25036108855692
A674K8RXXL	Black	56.0	42.0	40.0	0.1710	0.0941	5036108366569	25036108855715