



250 mm Adjustable Wrench - 1 pc

ADJUSTABLE WRENCHES

- Precision adjustment screw with accurate threads and tight tolerances. The jaws won't back off during use.
- Chrome plating for best-in-class rust protection and increased durability.
- Ergonomic rounded handle design for a comfortable fit in the hand and less pressure points on the palm.
- Slim head design for reaching into tight spaces.
- Parallel jaws won't slip or damage finish surfaces.
- Permanent lasered inch and mm markings for accurate adjustment
- 8" adjustable wrench (48227508) has an extra wide jaw of 38 mm for increased jaw capacity in confined environments.
- Lanyard hole.
- Available sizes: 150mm, 200mm, 200mm (wide), 250mm, 300mm, 380mm.
- Available packs: Twin, Triple.



Article Number	48227410, 4932499517
Jaw opening capacity for pipe (mm)	36.5
Jaw thickness [mm]	16
Pack quantity	1
Tip thickness [mm]	9,9
Total length (mm)	250
Total length [inch]	10
Weight (g)	535