

Datasheet

RS Pro Trace Heating Thermostat 75mm x 200mm x 150mm, 0 to +90 °C

RS Stock No: **665-7567**



Product Details

RS Pro trace heating thermostat measures 75 x 200 x 150 mm. This IP65 rated thermostat is moulded with PET/ABS for durability. It has a operating temperature range of 0 to +90°C. It is suitable for the termination and temperature control of trace heating systems for frost protection and process temperature maintaining of pipework and tanks.

Features and Benefits

- Designed for the termination and temperature control of trace heating systems for frost protection and process temperature maintaining of pipework and tanks
- Entries and terminations are provided for up to three trace heating circuits
- Easily adjustable temperature range dial with set temperature clearly visible
- Moulded PET/ABS
- IP65 rated

**Specifications:**

Dimensions	200 x 75 x 150 mm
Height	75 mm
Length	200 mm
Maximum Operating Temperature	+90°C
Minimum Operating Temperature	0°C
Operating Temperature Range	0 to +90°C
Type	Junction Box
Width	150 mm
Enclosure Material	ABS with PC Lid
IP Rating	IP65