

Hot air tool - Professional Line

PRO HM 2120 E Carwrapper Edition

EAN 4007841 089641

Article number 089641



series 5

2200 W

2200 W Output



80 – 630 °C



9 stage temperature
adjustment



150 - 500 l/min.



3 air volume levels



Suitable for pluggable
nozzles



VDE



CE

Function description

Experts in vehicle wrapping. Electronically controlled hot air tool HeatMatic 2120 E with 7.5 m cable. 2200 W, infinitely adjustable temperature from 80 – 630 °C, airflow rate adjustable from 150 – 500 l/min in 3 stages.

Technical specifications

Temperature	80 – 630 °C	Replaceable heating element	No
Airflow rate	150 – 500 l/min	Restart protection	No
Temperature setting	Continuous	Temperature scanner	Yes
Settings made via	Thumbwheel	Fine dust filter	No
Temperature display	Thumbwheel with labelled settings	Thermal cut-out	Yes
Airflow control	Settings	Thermostat	Yes
Programming function	No	ESD	No
Loc function	No	Nozzle receiver, type	34
Residual heat indicator	No	Cord length	7.5 m
Cool function	No	Dimensions (L x W x H)	253 x 87 x 200 mm
Motor, type	Brush motor	PU1, net weight	1,191 kg
Heating element	Ceramic heating element	Manufacturer's Warranty	1 year
Mains power supply	220 – 230 V / 50 – 60 Hz	PU1, EAN	4007841089641
Function, hanger	Yes	Output	2200 W
Function, life expectancy, motor	750 h	Product category	Hot air tool
Function, life expectancy, heating element	600 h		

<https://www.steinel.de>

Subject to technical modifications

03.2025 Page 1 from 2

Hot air tool - Professional Line

PRO HM 2120 E Carwrapping Edition

EAN 4007841 089641

Article number 089641



Accessories

EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 084189	Plastic squeegee - Alcantara
EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E
EAN 4007841 009601	Flexible hot air tool stand with suction pad foot