

T37 TUBULAR

SLD7308X2


7,5 W - 806lm - 2700K

20.000 H



15.000

INSTANT



DIMENSIONS	A	B	C
1	126	---	38

GENERAL INFORMATIONS	
Code	SLD7308X2
Ean	8031453017941
Family	T37 TUBULAR
Technology	LED
Energy class	A+
Operating temperature (° C)	-15 - +40

PACKAGING	
Packaging	BOX
Pack	10 / 50

LIGHTING DATA	
Kelvin (°)	2700
Lumen	806
Beam (°)	270
Luminous efficacy (lm / W)	107,46
Color rendering (CRI)	>80

TECHNICAL FEATURES	
Base	E14
Power (W)	7,5
Equivalence (W)	60
Supply voltage (V) / Max (V)	220 / 240
Power frequency (Hz)	50/60
Power factor	>0,55
Dimmer compatibility	NO