

VARTA Work Flex® Multifunction Light F20R Rechargeable



Compact allrounder for DIYers, (hobby) mechanics, and hands-on enthusiasts: Rechargeable multifunctional light with three light sources, integrated magnets and 180° folding function. Shock proof (2m), splash water and dust protected (IP54).



Information

- 3 light sources (main light, side light, spot light)
- 180° foldable design
- Water resistant (IP54) and shock proof (2m drop test)
- Compact and lightweight
- Pocket clip and magnet for hands free working
- Li-Ion rechargeable battery
- Low battery indicator (via flashes)
- Charging indicator
- Charging via USB Type C (cable incl.)
- VARTA Safety Features

Article Details

Ordernumber	18649 101 401
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	20.00 m
Runtime	6 h
Total light output	100 lm
Product Length / Depth mm	120.00
Product Width mm	19.20
Product Height mm	30.00
Product Weight g	61.00

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 057269	100.00	42.43	230.00	0.10
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	6	40 08496 070183	260.00	185.00	150.00	0.82
PAL (Pallet)	864	40 08496 070190	800.00	1,200.00	1,350.00	139.05
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
8	18		144		6	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

