

Push button head, Harmony XB5, plastic, flush, black, 22mm, spring return, clear boot, unmarked, grey bezel

ZB5APA2C0

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range of Product	Harmony XB5	
Product or Component Type	Head for non-illuminated push-button	
Device short name	ZB5	
Product Compatibility	Not compatible with legend holder	
Bezel material	Plastic colour plated grey	
Mounting diameter	0.9 in (22 mm)	
Head type	Standard	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	spring return	
Operator profile	Black flush, unmarked	
Operator additional information	Clear boot	

#### **Complementary**

•	,
CAD overall width	1.2 in (30 mm)
CAD overall height	1.2 in (30 mm)
CAD overall depth	1.5 in (37 mm)
Mechanical durability	10000000 cycles

### **Environment**

Protective treatment	тн	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Ambient air temperature for operation	-40158 °F (-4070 °C)	
Overvoltage category	Class II conforming to IEC 60536	
IP degree of protection	IP66 IEC 60529 IP67 IEC 60529	
NEMA degree of protection	NEMA 13 NEMA 4X	
Resistance to high pressure washer	1015.3 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
IK degree of protection	IK03 conforming to IEC 50102	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	IEC 60947-1	
	IEC 60947-5-1	
	IEC 60947-5-4	
	UL 508	
	JIS C8201-5-1	
	CSA C22.2 No 14	
	JIS C8201-1	
Product Certifications	CSA	
	DNV	
	BV	
	LROS (Lloyds register of shipping)	
	UL Listed	
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27	
	50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	

## Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
GTIN	3606489768485
Returnability	No
Country of origin	FR

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.65 in (4.2 cm)
Package 1 Width	1.30 in (3.3 cm)
Package 1 Length	2.05 in (5.2 cm)
Package 1 Weight	0.7 oz (19.0 a)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Use Again**

○ Repack and remanufacture		
Take-back	No	

Offer Marketing Illustration

#### **Product benefits / Features**

### **Technical Benefits**

#### Harmony XB5



Offer Marketing Illustration

#### **Product benefits / Features**



Image of product / Alternate images

**Alternative** 











