
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKS06MPN
COUPLING HALF: Coupler
CONNECTION TYPE: Tube
BODY MATERIAL: Brass
FUNCTION: Double Shut-Off
CONNECTION SIZE: 4x6 MM

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

TECHNOLOGY	Pneumatics
FLOW RATE	130 L/min (air)
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
FLOW RATE	1.2 L/min (water)
MINIMUM OPERATING TEMPERATURE	-4 °F
PRODUCT TYPE	Pneumatic Quick Couplings
VALVE TYPE	Standard Valve
REGION OF ORIGIN	Germany
WEIGHT	0.018 kg
INDUSTRY	Healthcare & Life Sciences
MAXIMUM OPERATING TEMPERATURE	212 °F
APPLICATION	Pharma
PLATING TYPE	Nickel-Plated
QUANTITY PER BOX	10.0
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
DIAMETER	2.7 mm (nominal)
MINIMUM OPERATING TEMPERATURE	-20 °C
CONNECTION TYPE	Tube Panel monted, without spring guard
DIVISION	Low Pressure Connectors Europe Division

OPERATION TYPE	Sleeve
PRODUCT SERIES	Series 20
INDUSTRY	General Industrial
MAXIMUM OPERATING TEMPERATURE	100 °C
HEX SIZE	12 mm (external)
BODY MATERIAL	Brass
PRODUCT STYLE	Quick Connect
CONNECTION SIZE	4x6 mm
MAXIMUM OPERATING PRESSURE	35 bar
COMPATIBLE FITTING	Series 20 Plug
FUNCTION	Double Shut-Off
INTERCHANGE TYPE	European Profile
MAXIMUM OPERATING PRESSURE	507 psi
APPLICATION	Medical
TECHNOLOGY	Fluid & Gas Handling
DIVISION	Low Pressure Connectors Europe Division
COUPLING HALF	Coupler
BRAND	Parker
APPLICATION	Industrial Machinery
VALVE INCLUDED	Yes
SEAL MATERIAL	NBR
BRAND	Rectus
LENGTH	45 mm
APPLICATION	Food & Beverages
SLEEVE MATERIAL	Brass