

TECHNICAL SHEET

POWER LED headlamp



1. Press to  turn on the headlamp and change modes
2. Press to  activate motion sensor mode.
3. Press for  3 seconds to activate flashing mode.



Rechargeable by USB
cable (Type-C charger)



Autonomy of 5 hours in
high power



(Charging time: 2h)
3.7V/1200mAh Li-battery



IPX4 rating: LEDs can be
used in heavy rain



350 Lumens
5 different lighting modes:
- Flashing
- High/Medium
- Side LED (high/medium)



Motion sensor mode
(On/Off)



Dust resistant



adaptable to
construction helmets



65 grams

www.surfex.eu