



ENGLISH

Datasheet

RS Pro Steel Alloy Compression Spring, 93.5mm x 11.25mm, 1.34N/mm

RS Stock No: 121-163



Product Details

RS Pro stainless steel alloy compression spring measures 93.5 x 11.25 mm and has a spring rate of 1.34 N/mm. It handles a load of 85.42 N at a minimum working length of 30 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Ground
Material	Steel Alloy
Free Length	93.5 mm
Load at Minimum Working Length	85.42 N
Minimum Working Length	30 mm
Outside Diameter	11.25 mm
Spring Rate	1.34 N/mm
Wire Diameter	1.25 mm