



HEAVY DUTY PLATFORM TRUCK, 24" X 48" WITH 8" TPR CASTERS

SKU: FG443600BLA



HEAVY DUTY PLATFORM TRUCK, 24" X 48" WITH 8" TPR CASTERS

The Heavy-Duty Platform Truck is ideal for moving large, heavy, oversized loads efficiently throughout a facility with up to 2,000 lb. capacity. Features a precision-engineered Duramold™ Deck constructed of resin and metal composite that is lighter than typical steel/wood products without sacrificing strength. Built tough and will not warp, dent, splinter, rust, or rot.



FEATURES & BENEFITS

- Designed with 2 fixed casters and 2 swivel casters for improved maneuverability
- 2,000 lb. capacity
- Variable grip-height handle improves control and worker safety
- Virtually maintenance-free - Powder-coated steel creates a hard finish that is far tougher than conventional paint
- Made in the USA
- Four molded in tie-down slots for securing loads with tie-down straps or bungees
- Duramold's exclusive, precision-engineered resin and metal composite structure provides maximum load support
- Textured deck surface reduces load slippage



HEAVY DUTY PLATFORM TRUCK, 24" X 48" WITH 8" TPR CASTERS

SKU: FG443600BLA

- Replacement parts: 3484156 - Crossbar Handle, 3485027 - Hardware Kit, FG4300L10000 - Lag Screws, FG4300L20000 - Bolt Kit, FG4403L30000 - Valco Clip, FG4436L80000 - 8" TPR Swivel & Fixed Caster Replacement Kit, FG4436M60000 - 8" Swivel Caster, FG4436M70000 - 8" Rigid Caster, FG4472L30000 - Work Height Hardware Kit, FG7907L1RED - Red Cross Bar Handle (For more info: visit www.specialmade.com)

SPECIFICATIONS

	U.S.	Metric
Product Length	48.00 in	121.92 cm
Product Width	24.00 in	60.96 cm
Product Height	9.00 in	22.86 cm
Product Weight	70.00 lb	31.75 kg
Case Pack Quantity	1	
Color	Black	
UPC	086876184464	

CERTIFICATIONS



MADE IN THE USA