

**ZM65** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M65X2	Thread
D	85 mm	Outside diameter
h	16 mm	Height
M _A	5 Nm	Mounting torque set screw
F _{aB}	280,000 N	Breaking load, axial
M _L	200 Nm	Breakawag
M _{AL}	120 Nm	Mounting torque reference
M _M	4.24 kg*cm ²	Mass moment of inertia
≈m	270 g	Weight

Dimensions

d ₁	78 mm	Plant diameter outside
t	3 mm	Hight retaining slot
b	7 mm	Width retaining slot
c	8 mm	Distance bore
m	M6	Threaded - threaded pin