



EMPTY ENCLOSURE

# AK-F 14 L-g



## AK-F 14 L-g

Empty enclosure

**CUSTOMIZE**

315 x 300 x 147 mm  
Article number: 73351001

Expansion enclosure / empty enclosure - Industrial Quality -, for small distribution boards AK-F 14-56, for individual expansion with standard rails or mounting plates, integrated ventilation elements to reduce the formation of condensate water, Un=400 V, Ui=1.000V AC / 1.500V DC, In=125A

with grey cover



## Technical data

### Measures

Width:	315 mm
Length:	300 mm
Height:	147 mm
Inner height:	122 mm
Inner width:	295 mm
Inner length:	310 mm

### Material:

Box:	polycarbonate, glass fiber-reinforced
------	--

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



---

EMPTY ENCLOSURE

## AK-F 14 L-g

---

### Other attributes

Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
Impact resistance:	IK08 acc. DIN EN 5012 / VDE 0470 segment 100
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1500 V
VDE mark of conformity:	DIN EN 60670