



### Main

Aesthetic name	M-Plan M-Elegance M-Star M-Plan glass M-Arc System M M-Smart
Device presentation	Mechanism with central plate
Outlet standard deviation	German
Product or component type	Socket-outlet
Socket additional information	With hinged lid

### Complementary

Outlet poles configuration	2P + E
Wiring device mounting	Flush
Fixing mode	By screws and claws
Colour tint	Polar white (RAL 9010)
Connections - terminals	Screwless terminals
Rated current	16 A
[Ue] rated operational voltage	250 V

### Environment

IP degree of protection	IP44
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins