

**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

Cordless Impact Driver

## GDR 18V-200



Best combination of power and size with 1/4" bit holder

### The most important data

Torque, max.	200 Nm
Screw diameter	M 6 – M 16
Weight excl. battery	1.1 kg

**Part Number** 0 601 9J2 106[> More product information](#)

## Technical data

### Technical data

No-load speed	0-3,400 rpm
Weight excl. battery	1.1 kg
Torque, max.	200 Nm
Impact rate	0-4,000 bpm
Tool holder	1/4" Hex Uni
Breakaway torque, max.	350 Nm

### 'Total vibration values (Tightening screws and nuts of maximum permitted size)'

Vibration emission value ah	14 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Screw diameter

Screw diameter	M 6 – M 16
----------------	------------

## Noise/vibration information

### Tightening screws and nuts of maximum permitted size

Vibration emission value ah	14 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Compact head length of 126 mm for working in tight spaces
- Strong 200 Nm tightening torque, 350 Nm breakaway torque, excellent battery runtime and long tool lifespan due to the brushless motor
- Variable speed trigger for better control over speed and torque

