



Datasheet

Stock No: 267-4079

ENGLISH

RS Pro Hooked Insulated Crimp Blade Terminal 17.4mm Blade Length, 16 → 14 AWG, Blue



Product Details:

Hook Blade

Red 0.5 - 1.5 mm²

Blue 1 - 2.6 mm²

Yellow 2.5 - 6.5 mm²

Note

For Hook blades (see stock no. 267-4063) the overall lengths are 27.4 (red), 28.4 (blue) and 30.2 (yellow). Size quoted is blade width.

Approvals

UL Listed; UL Listed for Canada

Specifications:

Gender: Male
 Wire Size: 16 → 14 AWG
 Hooked: Yes
 Insulation: Insulated
 Shrouded: Unshrouded
 Insulation Material: Nylon
 Colour: Blue
 Overall Length: 28.2mm
 Inner Diameter: 5.2mm
 Blade Length: 17.4mm
 Blade Width: 3mm
 Blade Thickness: 0.8mm
 Contact Material: Copper
 Contact Plating: Tin

Temperature rating:	-55°C to 105°C
Terminal Material:	
Receptacles	High grade brass
Other terminals	High grade copper
Voltage rating	
Brass	300V
Copper	600V
Additional Sleeve Material:	High grade copper

