

HyFlex®

ADVANCED MECHANICAL PROTECTION

70-750

Premium longevity and cut protection through advanced technology

Previously known as: Vantage70-750



Cut



Heavy Duty

Medium duty cut resistant gloves with dot grip

These premium gloves use innovative technology for improved cut resistance, excellent flexibility and a higher level of comfort.



Industries

- Automotive
- Metal fabrication
- Machinery and Equipment

Applications

- Assembling metal parts and components
- Body assembly
- Handling sharp or irregular metal pieces

Previously known as: Vantage70-750

Key Features

- The optimal combination of cut resistance, comfort and dexterity. Looking for maximum cut protection combined with superior longevity? Ansell's HyFlex® range is the solution. These premium gloves use innovative technology for improved cut resistance, excellent flexibility and a higher level of user comfort.
- High performance redefined. Reserved exclusively for our premium gloves, Ansell's cut resistance technology uses revolutionary engineered yarns with the highest cut-protection-to-weight ratio available. This makes the HyFlex® gloves ideal for handling sharp tools and materials.

Performance Standards & Regulatory Compliance

REACH Compliant

EN388: 2016



2X4XD

EN 407



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 70-750	Liner Material: Kevlar®, Lycra®, Stainless steel, Ansell INTERCEPT™ Technology Cuff Style: Knitwrist	13	7, 8, 9, 10	230-270 mm	• 12 pairs per polybag; 12 polybags per carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalin Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.