

## FEATURES

- **UV Resistant:** Ensures longevity and performance in outdoor conditions.
- **High Tensile Strength:** Supports up to 36 kg, providing robust cable management.
- **Nylon Material:** Offers durability and flexibility for various applications.
- **300 mm Length:** Suitable for bundling larger cable groups.
- **UL 94 V-2 Fire Behaviour:** Provides a level of flame retardancy for safety.
- **RoHS Compliant:** Meets environmental and safety standards.

## RS PRO UV Protected Cable Tie, 300 mm Length

RS Stock No: 656-044



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO UV Protected Cable Ties are designed for securing and organising cables in various environments. Made from durable nylon, they offer excellent resistance to UV light, making them ideal for outdoor applications. With a maximum bundle diameter of 83 mm, they provide a reliable solution for managing large cable groups.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	UV Protected Cable Tie
Tensile Strength	36 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

### Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	83 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---