



ENGLISH

Datasheet

## RS Pro Magnetic Lock, 1670N

RS Stock No: **739-3233**



### Product Details

RS Pro magnetic lock provides a holding force when de-energised and release when pulsed. This electromagnetic lock offers 1670 N dynamic holding force capacity and is suitable for typical applications such as machine mechanisms, door/guard locking and remote hold/release requirements.

### Features and Benefits

- Holding force of 1670 N
- Suitable for typical applications such as machine mechanisms, door/guard locking and remote hold/release requirements
- Provides a holding force when de-energised and release when pulsed



ENGLISH

### Specifications:

AC or DC Operation	DC
Diameter	65 mm
Holding Force	1670 N
Length	111 mm
Supply Voltage	24 V dc
Depth	35 mm
Application	Machine Mechanisms, Door/Guard Locking & Remote Hold/Release Requirements
Current Rating	340 mA
Finish	Bright Nickel Plated with Machined Face
IP Rating	IP20
Power Consumption	8.2 W