

*JST*

Hand crimping tool  
Type: WC-260

Features

Parallel action  
operation

Ratchet release

Easy readjustment  
of load

Contact locator with  
insulation-stop

Precisely ground  
profiles

Ergonomic soft grips  
colour: green

Fully recyclable

Applicable terminal:  
< >EH-001T-0.6

Cross section range:  
Profile 1: 30 AWG  
Profile 2: 26 AWG/28 AWG  
Profile 3: 22 AWG/24 AWG

Crimp height specification  
30 AWG - 0.57-0.62mm  
28 AWG - 0.60-0.65mm  
26 AWG - 0.60-0.70mm  
24 AWG - 0.65-0.75mm  
22 AWG - 0.70-0.80mm

Operating instructions see overleaf

